

CEREFORM[®] APTMA

PROFILES

LOW PROFILE Round Low (RL)

Volume 100 to 500 cc

Projection
2,3 cm
to
4,3 cm

Diameter
9,2 cm
to
15,3 cm

MEDIUM PROFILE Round Medium (RM)

Volume 100 to 700 cc

Projection
2,5 cm
to
5,9 cm

Diameter
8,9 cm
to
16,0 cm

HIGH PROFILE Round High (RH)

Volume 125 to 700 cc

Projection
3,2 cm
to
6,9 cm

Diameter
8,8 cm
to
14,9 cm

VERY HIGH PROFILE Round Very High (RVH)

Volume 130 to 900 cc

Projection
4,0 cm
to
8,2 cm

Diameter
8,2 cm
to
15,0 cm

REFERENCES

Volumes over 500 cc. available
on order and subject to a surcharge

LOW PROFILE Round Low (RL)

Volume (cc)	Projection (cm)	Diameter (cm)	Smooth Reference	Micro-textured reference
100	2,3	9,2	RLS100	RLMV100
125	2,5	9,9	RLS125	RLMV125
150	2,6	10,4	RLS150	RLMV150
175	2,8	11,0	RLS175	RLMV175
200	2,9	11,4	RLS200	RLMV200
220	3,1	11,8	RLS220	RLMV220
240	3,2	12,1	RLS240	RLMV240
260	3,3	12,4	RLS260	RLMV260
280	3,4	12,7	RLS280	RLMV280
300	3,5	13,0	RLS300	RLMV300
325	3,7	13,3	RLS325	RLMV325
350	3,8	13,6	RLS350	RLMV350
400	4,0	14,2	RLS400	RLMV400
450	4,2	14,8	RLS450	RLMV450
500	4,3	15,3	RLS500	RLMV500

MEDIUM PROFILE Round Medium (RM)

Volume (cc)	Projection (cm)	Diameter (cm)	Smooth Reference	Micro-textured reference
100	2,5	8,9	RMS100	RMVM100
125	2,7	9,6	RMS125	RMVM125
150	2,9	10,1	RMS150	RMVM150
175	3,1	10,6	RMS175	RMVM175
200	3,3	11,0	RMS200	RMVM200
220	3,4	11,4	RMS220	RMVM220
240	3,6	11,6	RMS240	RMVM240
260	3,8	11,9	RMS260	RMVM260
280	3,9	12,2	RMS280	RMVM280
300	4,1	12,5	RMS300	RMVM300
325	4,3	12,8	RMS325	RMVM325
350	4,4	13,1	RMS350	RMVM350
375	4,5	13,3	RMS375	RMVM375
400	4,7	13,6	RMS400	RMVM400
450	5,0	14,1	RMS450	RMVM450
500	5,2	14,6	RMS500	RMVM500
550	5,3	14,9	RMS550	RMVM550
600	5,5	15,3	RMS600	RMVM600
650	5,7	15,7	RMS650	RMVM650
700	5,9	16,0	RMS700	RMVM700

HIGH PROFILE Round High (RH)

Volume (cc)	Projection (cm)	Diameter (cm)	Smooth Reference	Micro-textured reference
125	3,2	8,8	RHS125	RHMV125
150	3,4	9,3	RHS150	RHMV150
175	3,7	9,8	RHS175	RHMV175
200	3,9	10,2	RHS200	RHMV200
225	4,2	10,5	RHS225	RHMV225
250	4,4	10,9	RHS250	RHMV250
275	4,6	11,2	RHS275	RHMV275
300	4,8	11,5	RHS300	RHMV300
325	5,0	11,8	RHS325	RHMV325
350	5,1	12,1	RHS350	RHMV350
375	5,3	12,3	RHS375	RHMV375
400	5,4	12,6	RHS400	RHMV400
425	5,6	12,7	RHS425	RHMV425
450	5,7	13,0	RHS450	RHMV450
500	6,0	13,4	RHS500	RHMV500
550	6,1	13,8	RHS550	RHMV550
600	6,3	14,2	RHS600	RHMV600
650	6,6	14,6	RHS650	RHMV650
700	6,9	14,9	RHS700	RHMV700

VERY HIGH PROFILE Round Very High (RVH)

Volume (cc)	Projection (cm)	Diameter (cm)	Smooth Reference	Micro-textured reference
130	4,0	8,2	RVHS130	RVHMV130
150	4,4	8,7	RVHS150	RVHMV150
190	4,6	9,2	RVHS190	RVHMV190
220	4,9	9,6	RVHS220	RVHMV220
250	5,3	10,0	RVHS250	RVHMV250
280	5,4	10,3	RVHS280	RVHMV280
310	5,7	10,6	RVHS310	RVHMV310
340	5,9	10,9	RVHS340	RVHMV340
370	6,0	11,2	RVHS370	RVHMV370
400	6,3	11,5	RVHS400	RVHMV400
450	6,6	11,9	RVHS450	RVHMV450
500	6,8	12,3	RVHS500	RVHMV500
550	7,0	12,6	RVHS550	RVHMV550
600	7,2	12,9	RVHS600	RVHMV600
650	7,4	13,2	RVHS650	RVHMV650
700	7,7	13,5	RVHS700	RVHMV700
750	7,9	13,8	RVHS750	RVHMV750
800	8,1	14,1	RVHS800	RVHMV800
900	8,2	15,0	RVHS900	RVHMV900

Range of silicone gel-filled breast implants more cohesive than the traditional range and offering better implant holding. It allows you to offer your patient slightly greater projections for the same diameter.